

**Ciljna skupina**

Zahtjev za dodatni fokus na blizinu u gornjem dijelu leće. Životna dob 45+.

Način izrade

Unutarnja progresivna površina, vidno polje u gornjem dijelu leće promjera 35 mm za fokus na blizinu.

Optimizacija

Specijalno tanjenje za leću u plus rasponu na osnovu oblika okvira i parametra za fitovanje leće u okvir. Ako se lećaporučuje bez opcije Optimizacija, topografija leće bit će decentrirana nazalno u odnosu na geometrijsko središte za 2,5 mm.

Tehnologija

IOT Endless Pilot Progressive

Poručivanje dioptrije

1/4, 1/8, 1/100

Individualni parametri

IPD, PL, Vertex, Panto, Ztilt, NVD

Inset

Po potrebi od 0 do 4 ili automatski izračun ineta.

Progresivna duljina

14 mm, 16 mm, 18 mm

Minimalna visina ugradnje

16 mm, 18 mm, 20 mm

Način poručivanja

- Dioptrija daljina/blizina
- Adicija od 1.00 do 3.00
- Gornji fokus "60/100" ili "80/100"

Preporuka za prodaju:

60/100 – kada se rad obavlja na distanci od 1 m
80/100 – kada se rad obavlja na distanci od 0,40 m

Način fitovanja (za preciznu ugradnju)

Oznaku za fitovanje centrirati na zjenicu. Preporučeno odstojanje od zjenice do gornjeg ruba okulara 14 mm.

Ocjene korisnika

Vid – daljina



Vid – blizina



Spontano privikavanje



Vid – srednja daljina




Udobnost tijekom korištenja



Korištenje elektroničkih uređaja

**Oznake na lećama**

■ gravire
■ markeri

**MATERIJALI**

1.50 CR-39	1
1.53 Trivex	2
1.59 Poly	4
1.60 High Index	5
1.60 Tribrid	6
1.67 High Index	7
1.74 High Index	8

DORADE

Bez dorade	W	Transitions GEN 8 Sapphire	F	Nupolar Gray	S
Remuve 400	H	Transitions GEN 8 Amethyst	M	Nupolar Gray Light	L
Remuve 420	R	Transitions GEN 8 Amber	A	Nupolar Green	E
Remuve 420 Photomatic Brown	O	Transitions GEN 8 Emerald	E	Transitions XTRActive Polarised Gray	X
Remuve 420 Photomatic Gray	U	Transitions XTRActive Brown	C	DriveWear	D
Transitions GEN 8 Brown	Z	Transitions XTRActive Gray	L		
Transitions GEN 8 Gray	N	Transitions XTRActive Green	K		
Transitions GEN 8 Green	V	Nupolar Brown	B		