



Ciljna skupina

Iskusni poznavatelji progresivne leće.
Životna dob 45+.

Tehnologija

OPTOTECH Extended IXL

Način izrade

Unutarnja izrada progresivne površine.

Poručivanje dioptrija

1/4

Individualni parametri

IPD, PL, Vertex, Panto, Ztilt, NVD

Inset

Po potrebi od 0 do 4 ili automatski
izračun inseta.

Progresivna duljina

15 mm, 16 mm, 17 mm, 18 mm, 19 mm ili
varijabilna u odnosu na visinu fitovanja.

Minimalna visina ugradnje

17 mm, 18 mm, 19 mm, 20 mm,
21 mm

Optimizacija

Specijalno tanjenje za leću u plus
rasponu na osnovu oblika okvira i
parametra za fitovanje leće u okvir.
Ako se leća poručuje bez opcije
Optimizacija, topografija leće bit će
decentrirana nazalno u odnosu na
geometrijsko središte za 2,5 mm.

Ocjene korisnika

Vid – daljina



Vid – blizina



Spontano privikavanje



Vid – srednja daljina



Udobnost tijekom korištenja




Korištenje elektroničkih uređaja



Oznake na lećama

■ gravire
■ markeri



MATERIJALI

1.50 CR-39	1
1.53 Trivex	2
1.56 Mid. index	3
1.59 Poly	4
1.60 High Index	5
1.60 Tribrid	6
1.67 High Index	7
1.74 High Index	8

DORADE

Bez dorade	W	Transitions GEN 8 Sapphire	F	Nupolar Gray	S
Remove 400	H	Transitions GEN 8 Amethyst	M	Nupolar Gray Light	L
Remove 420	R	Transitions GEN 8 Amber	A	Nupolar Green	E
Remove 420 Photomatic Brown	O	Transitions GEN 8 Emerald	E	Transitions XTRActive Polarised Gray	X
Remove 420 Photomatic Gray	U	Transitions XTRActive Brown	C	Photomatic Brown	B
Transitions GEN 8 Brown	Z	Transitions XTRActive Gray	L	Photomatic Gray	I
Transitions GEN 8 Gray	N	Transitions XTRActive Green	K	DriveWear	D
Transitions GEN 8 Green	V	Nupolar Brown	B		